

PRINTGUARD^{PLUS} JACKETS FOR HEIDELBERG[®] PRESS TRANSFER CYLINDERS


Stop Marking
Stop Marking
Stop Marking

● Start **Printing**

with

PrintGuard^{plus}

Orange Hide[®]
Microcellular Backed
AntiMarking Products



**PrintGuardPlus Orange Hide
Anti-Marking Jackets
for Heidelberg[®] Presses.**

Ask for PrintGuardPlus Jackets containing our patented resilient microcellular backing material. These PrintGuardPlus Orange Jackets have custom fixtures for quick and easy installation. Our jackets fit perfectly on the cylinder. Typically, no additional packing is needed. PrintGuard's high quality anti-marking jackets are guaranteed to improve your print quality, customer satisfaction, press-up-time, and your bottom line!

PATENTED MICROCELLULAR LAYER

US Patent Nos. 6,811,863 7,270,873, others pending

PrintGuardPlus = Orange Hide + Microcellular Backing


PrintGuardPlus Orange Jackets. Why we are #1

- **Orange Hide:** A cross linked orange silicone coating reduces the surface energy of the PrintGuard glass beaded surface. This means that ink does not want to stick to the Orange Hide surface. Less ink attraction = less marking = more profit. We apply 2x as much silicone as our competition.
- **Microcellular Backing:** OUR PATENTED microcellular backing provides a compressible layer that ensures the surface of the glass beads lay perfectly flat and uniform across your entire cylinder – no more bubbles, ridges, or voids that can cause marking! And, in most cases, no additional packing is required.
- **Secure-Safe™ Stainless Steel Hardware / Elastic Loops:** Durable elastic loops resistant to oils and solvents. They stretch just the right amount to allow for quick and easy attachment to your Heidelberg transfer/delivery cylinder. For SM-52, SM-74 and SM-102 (post 1993), our patent pending Secure-Safe™ stainless steel hardware with brass rivets are affixed to one or both jacket ends for a custom cylinder fit. Our Secure-Safe™ double fixturing method ensures the jacket is safely secured to your transfer cylinder.

PrintGuard's mission is to develop and manufacture the most innovative, highest quality products that make printers more profitable.

**PrintGuardPlus
Orange
Jacket Material**

Orange Hide Microcellular Backed Material used for Transfer & Delivery Jackets for all Heidelberg presses.
Thickness: 41mils / 1.04mm



This brochure was printed by Craftsmen using PrintGuard products.

PRINTGUARD^{PLUS} JACKETS FOR HEIDELBERG[®] PRESS TRANSFER CYLINDER

Stop Marking
Stop Marking
Stop Marking

• Start **Printing**

with

PrintGuard^{plus}

Orange Hide[®]
Microcellular Backed
AntiMarking Products




PATENTED MICROCELLULAR LAYER


US Patent Nos. 6,811,863 7,270,873, others pending




PrintGuard^{Plus} Orange Jackets
for Heidelberg Presses




QM46V Jacket
for Heidelberg QM46 press




GT052T Jacket
for Heidelberg GT052 press



M026T Jacket
for Heidelberg MOV press




SM72T Jacket
for Heidelberg SM72 press




SM102LL Jacket
for Heidelberg SM102 press
(pre-1993)

SM74T Jacket
for Heidelberg SM-74 press



Mechanically fixed
to ensure Secure-Safe™
performance on press

Patented
Microcellular Layer
for perfect fit



SM102RL Jacket
for Heidelberg SM-102 press
(post-1994)



Orange Hide Ink
repellent coating over durable
glass bead matrix

SM52T Jacket
for Heidelberg SM52 press

Delivery and Perfecting Jackets also made to fit on Heidelberg Presses.

NEW Perfector Cylinder Jackets for Mitsubishi 3000D Press

Custom Jackets Made Upon Request.

Both Heidelberg and GTO are registered trademarks respectively, trademarks of Heidelberger Druckmaschinen AG in the U.S. and/or other countries.

PrintGuard Guarantee

The manufacturer and technical sales team stand behind PrintGuard's Performance! Buy two PrintGuardPlus jackets to confirm for yourself that PrintGuard will actually save you money by decreasing your press downtime and improving your print quality. Follow care and maintenance instructions below and if you are not satisfied with PrintGuard's performance, simply return these jackets within one month and we will refund the full product price.

PrintGuard, Inc.

1521 Grafton Road, Millbury, MA 01527
Phone: (508) 890-8822 • Fax: (508) 890-8833

Website: www.antimarking.com

E-Mail: techspt@antimarking.com

Care & Maintenance:

For longest product life, inspect daily—if clean leave alone; Else:

1. Use the PrintGuard Cleaning Cloth (Or cotton shop cloth).
2. Moisten Cloth with a mild press-wash, preferably water based or diluted 50/50 with water.
3. Use uniform light pressure to remove wet ink.

PrintGuard, Orange Hide, and PrintGuardPlus are registered trademarks of PrintGuard, Inc. in the U.S. and/or other countries. Press manufacturers are not affiliated with PrintGuard, Inc., and may have rights in the names listed. Heidelberg and GTO are registered trademarks respectively of Heidelberger Druckmaschinen AG.

CONTACT YOUR LOCAL DEALER AT: